

# Eaton CH24B150E

Catalog Number: CH24B150E

CH 3/4-inch loadcenter, Main breaker, 150A, E, Copper, Ch8ef-combination, ch8es-surface, not included, NEMA 1, Metallic, 25 kAIC, CSR, 24, 24, Three-wire, Single-phase, #2/0 AWG-300 kcmil, Top/bottom



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CH24B150E
<b>UPC</b>	<b>Product Length/Depth</b>
782113097756	29.13 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
15 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

## Product specifications

### Type

Main breaker

### Amperage Rating

150 A

### Bus material

Copper

### Cover

Ch8ef-combination, ch8es-surface, not included

### Main circuit breaker

CSR

### Number of circuits

24

### Number of spaces

24

### Phase

Single-phase

### Wire size

#2/0 AWG-300 kcmil

### Feed type

Top/bottom

### Box size

E

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH24B150E

### Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)