

Eaton CH24B200R

Catalog Number: CH24B200R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 200 A, E, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 24, 24, Three-wire, Single-phase, #2/0 AWG-300 kcmil, Overhead, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH24B200R
UPC	Product Length/Depth
782113097787	29.13 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
15.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22. Loadcenter contains single insulated/bondable neutral.

Product specifications

Special features

Cover included

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

24

Number of spaces

24

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Feed type

Overhead

Voltage rating

120/240 V

Box size

E

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH24B200R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)