

Eaton CH24L125R

Catalog Number: CH24L125R

Eaton CH main lug loadcenters, Standard, Main lug only, 125A, C, Copper, NEMA 3R, Metallic, Overhead, CH, 24, 24, Three-wire, Single-phase, 120/240 V, #6-2/0 AWG



General specifications

Product Name

Eaton CH main lug loadcenter

Catalog Number

CH24L125R

UPC

782113097701

Product Length/Depth

21 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

15 lb

Warranty

Limited lifetime

Certifications

UL 50

UL 67

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main lug only

Amperage Rating

125 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

24

Number of spaces

24

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#6-2/0 AWG

Box size

C

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH24L125R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)