

Eaton CH2L70RP

Catalog Number: CH2L70RP

Eaton CH main lug loadcenters, Standard, Main lug only, 70A, 5r, Copper, NEMA 3R, Metallic, Overhead, CH, 2, Four-pole, 2, Three-wire, Single-phase, 120/240 V, #14-2 AWG



General specifications

Product Name

Eaton CH main lug loadcenter

Catalog Number

CH2L70RP

UPC

782114190456

Product Length/Depth

9.5 in

Product Height

3.13 in

Product Width

4.5 in

Product Weight

5.25 lb

Warranty

Limited lifetime

Certifications

UL 50

UL 67

Catalog Notes

Ground bar kits priced separately.
Suitable for use as service equipment when not more than two service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main lug only

Amperage Rating

70 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

2

Number Of Poles

Four-pole

Number of spaces

2

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#14-2 AWG

Box size

5R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Type CH Circuit Breakers and Loadcenters

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH2L70RP



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)