

Eaton CH30L3150R

Catalog Number: CH30L3150R

Eaton CH main lug loadcenter, Standard, Main lug only, 150 A,D, Copper, NEMA 3R, Metallic, Overhead, CH, 30 Circuits, 30 Spaces, Four-wire, Three-phase, #4 AWG-300 kcmil



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH30L3150R
UPC	Product Length/Depth
782113097916	29.13 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
34.8 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Furnished with hub closure plates.

Product specifications

Special features

Standard

Type

Main lug only

Amperage Rating

150 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

30

Number of spaces

30

Phase

Three-phase

Wire size

#4 AWG-300 kcmil

Box size

D

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

35 kAIC

Number of wires

4

Resources

Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH30L3150R

Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CH30L3150R

Catalog Number: CH30L3150R

Eaton CH main lug loadcenter, Standard, Main lug only, 150 A,D, Copper, NEMA 3R, Metallic, Overhead, CH, 30 Circuits, 30 Spaces, Four-wire, Three-phase, #4 AWG-300 kcmil



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH30L3150R
UPC	Product Length/Depth
782113097916	29.13 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
34.8 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Furnished with hub closure plates.

Product specifications

Special features

Standard

Type

Main lug only

Amperage Rating

150 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

30

Number of spaces

30

Phase

Three-phase

Wire size

#4 AWG-300 kcmil

Box size

D

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

35 kAIC

Number of wires

4

Resources

Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH30L3150R

Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)