



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH32B150J

UPC:782113098081

Dimensions:

- **Height:** 3.88 IN
- **Length:** 34.13 IN
- **Width:** 14.31 IN

Notes: Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Standard
- **Type:** Main breaker
- **Amperage Rating:** 150A
- **Box Size:** J
- **Bus Material:** Copper
- **Cover:** Ch8jf-combination, ch8js-surface, not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 32
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2/0 AWG-300 kcmil
- **Feed Type:** Top/bottom

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)



- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - CH32B150J](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH32B150J

UPC:782113098081

Dimensions:

- **Height:** 3.88 IN
- **Length:** 34.13 IN
- **Width:** 14.31 IN

Notes: Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Standard
- **Type:** Main breaker
- **Amperage Rating:** 150A
- **Box Size:** J
- **Bus Material:** Copper
- **Cover:** Ch8jf-combination, ch8js-surface, not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 32
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2/0 AWG-300 kcmil
- **Feed Type:** Top/bottom

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eaton's Volume 1-Residential and Light Commercial](#)



- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - CH32B150J](#)

Certifications:

- UL 50
- UL 67

Product compliance: No Data

© 2016 Eaton. All rights reserved.