

Eaton CH32B225R

Catalog Number: CH32B225R

Eaton CH main breaker loadcenters, Standard, Main breaker, 225 A, J, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 32, 32, Three-wire, Single-phase, #2/0 AWG-300 kcmil, Overhead, 120/240 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH32B225R
UPC	Product Length/Depth
782113098159	34.13 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
15.812 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22.
UL 50	Loadcenter contains single insulated/bondable neutral.

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main breaker

Amperage Rating

225 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Feed type

Overhead

Voltage rating

120/240 V

Box size

J

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH32B225R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)