

# Specifications

Photo is representative

## Eaton CH32BPN200J

CH 3/4-inch loadcenter, Plug-on neutral, Main breaker, 200A, J, Copper, Ch8jf-combination, ch8js-surface, not included, NEMA 1, Metallic, 35 kAIC, CSH, 32, 32, Three-wire, Single-phase, #2/0 AWG-300 kcmil

### General specifications

<b>PRODUCT NAME</b>	Eaton CH main breaker loadcenter
<b>CATALOG NUMBER</b>	CH32BPN200J
<b>UPC</b>	782116983377
<b>PRODUCT LENGTH/DEPTH</b>	34.13 in
<b>PRODUCT HEIGHT</b>	3.88 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	15.8 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 67 UL 50
<b>CATALOG NOTES</b>	Single phase convertible loadcenters with main breaker included

## Product specifications

<b>SPECIAL FEATURES</b>	Plug-on neutral
<b>TYPE</b>	Main breaker
<b>AMPERAGE RATING</b>	200 A
<b>BUS MATERIAL</b>	Copper
<b>COVER</b>	Ch8jf-combination, ch8js-surface, not included
<b>MAIN CIRCUIT BREAKER</b>	CSH
<b>NUMBER OF CIRCUITS</b>	32
<b>NUMBER OF SPACES</b>	32
<b>PHASE</b>	Single-phase
<b>WIRE SIZE</b>	#2/0 AWG-300 kcmil
<b>BOX SIZE</b>	J
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	35 kAIC
<b>NUMBER OF WIRES</b>	3

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>MULTIMEDIA</b>	<a href="#">AFCI Educational Video</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CH32BPN200J</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

