

Eaton CH32N200R

Catalog Number: CH32N200R

Eaton CH 3/4-inch loadcenter, single-phase, 32 circuits, 32-pole, #2/0-300 kcmil wire, 200A, NEMA 3R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CH32N200R
UPC	Product Length/Depth
782113098531	34.13 in
Product Height	Product Width
5 in	14.31 in
Product Weight	Warranty
35.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 50	Furnished with hub closure plates.
UL 67	

Product specifications

Special features

Standard

Type

Convertible

Amperage Rating

200 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Box size

J

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH32N200R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)