

Eaton CH42B200R

Catalog Number: CH42B200R

Eaton CH main breaker loadcenters, Standard, Main breaker, 200 A, K, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 42, 42, Three-wire, Single-phase, #2 AWG-300 kcmil, Overhead, 120/240 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH42B200R
UPC	Product Length/Depth
782113098227	37 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
15.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Furnished with hub closure plates.
UL 50	Loadcenter contains single insulated/bondable neutral.

Product specifications

Special features

Standard

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

42

Number of spaces

42

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Feed type

Overhead

Voltage rating

120/240 V

Box size

K

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH42B200R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CH42B200R

Catalog Number: CH42B200R

Eaton CH main breaker loadcenters, Standard, Main breaker, 200 A, K, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 42, 42, Three-wire, Single-phase, #2 AWG-300 kcmil, Overhead, 120/240 V



Photo is representative

General specifications

Product Name

Eaton CH main breaker loadcenter

Catalog Number

CH42B200R

UPC

782113098227

Product Length/Depth

37 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

15.5 lb

Warranty

Limited lifetime

Certifications

UL 67

UL 50

Catalog Notes

Furnished with hub closure plates.

Loadcenter contains single insulated/bondable neutral.

Product specifications

Special features

Standard

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

42

Number of spaces

42

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Feed type

Overhead

Voltage rating

120/240 V

Box size

K

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH42B200R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)