



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch main loadcenter

CH42B225K

UPC:782114227473

Dimensions:

- **Height:** 3.88 IN
- **Length:** 37 IN
- **Width:** 14.31 IN

Notes: Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Standard
- **Type:** Main breaker
- **Amperage Rating:** 225A
- **Box Size:** K
- **Bus Material:** Copper
- **Cover:** Ch8kf-combination, ch8ks-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 42
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2-300 kcmil
- **Feed Type:** Overhead or underground

Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton's Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - CH42B225K](#)
- [Dimensional Drawing - CH 3/4 LOADCENTER,](#)



CSR MAIN BREAKER, INDOOR NEMA 1,
120/240 VAC, 1 PHASE

Certifications:

- UL 50
- UL 67

Product compliance: No Data

© 2016 Eaton. All rights reserved.