

Eaton CH42BPN200K

Catalog Number: CH42BPN200K

CH 3/4-inch main loadcenter, Plug-on neutral, Main breaker, 200A, K, Copper, Ch8jf-combination, ch8js-surface, NEMA 1, Metallic, 35 kAIC, CSH, 42, 42, Three-wire, Single-phase, #2/0 AWG-300 kcmil



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH42BPN200K
UPC	Product Length/Depth
782116983384	37 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Single phase convertible loadcenters with main breaker included

defaultTaxonomyAttributeLabel

Special features

Plug-on neutral

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Cover

Ch8jf-combination, ch8js-surface

Main circuit breaker

CSH

Number of circuits

42

Number of spaces

42

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Box size

K

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

35 kAIC

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH42BPN200K



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)