

Eaton CH4L125FP

Catalog Number: CH4L125FP

Eaton CH main lug loadcenters, Standard, Main lug only, 125A, 7, Copper, NEMA 1, Metallic, Top/bottom, CH, Flush, 2, Eight-pole, 4, Three-wire, Single-phase, 120/240 V, #14-1/0 AWG



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH4L125FP
UPC	Product Length/Depth
782114190494	13 in
Product Height	Product Width
3.69 in	11 in
Product Weight	Warranty
12.4 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Ground bar kits priced separately. Suitable for use as service equipment when not more than two service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main lug only

Amperage Rating

125 A

Bus material

Copper

Feed type

Top/bottom

Main circuit breaker

CH

Mounting

Flush

Number of circuits

2

Number Of Poles

Eight-pole

Number of spaces

4

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#14-1/0 AWG

Box size

7

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH4L125FP

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia