
# Eaton CH4L125SP

# Catalog Number: CH4L125SP

Eaton CH main lug loadcenters, Standard, Main lug only, 125A, 7, Copper, NEMA 1, Metallic, Top/bottom, CH, Surface, 4, Eight-pole, 4, Three-wire, Single-phase, 120/240 V, 208 Y/120, 240 V, #14-1/0 AWG





#### Product Name

Eaton CH main lug loadcenter

#### **UPC**

782114190500

#### **Product Height**

3.69 in

### **Product Weight**

12.4 lb

#### Certifications

UL 67 UL 50

# Catalog Number

CH4L125SP

#### Product Length/Depth

13 in

#### **Product Width**

11 in

#### Warranty

Limited lifetime

# Catalog Notes

Ground bar kits priced separately.

Suitable for use as service equipment when not more than two service disconnecting mains are provided or when not used as a lighting and appliance panelboard.



# defaultTaxonomyAttributeLabel

Special features

Main lug only

**Amperage Rating** 

Standard

Type

125 A

Bus material Copper Feed type Top/bottom Main circuit breaker CH Mounting Surface Number of circuits 4 **Number Of Poles** Eight-pole Number of spaces 4 Phase Single-phase Voltage rating 120/240V, 208Y/120, 240V Wire size #14-1/0 AWG Box size 7 **Enclosure** NEMA 1 **Enclosure material** Metallic Interrupt rating 25 kAIC

# Resources

#### **Brochures**

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

# Catalogs

Eaton's Volume 1—Residential and Light Commercial

#### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

#### Multimedia

AFCI Educational Video

# Specifications and datasheets

Eaton Specification Sheet - CH4L125SP



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia