



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch main loadcenter

**CH60BPN200N**

**UPC:**786685425276

### Dimensions:

- **Height:** 3.88 IN
- **Length:** 45 IN
- **Width:** 14.31 IN

**Notes:**Requires the use of type chnt breakers. Main breaker plug-on neutral loadcenter. 225A max.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Plug-on neutral
- **Type:** Main breaker
- **Amperage Rating:** 200A
- **Box Size:** N
- **Bus Material:** Copper
- **Cover:** Ch8nf- combination, not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 35 kAIC
- **Main Circuit Breaker:** CSH
- **Number Of Circuits:** 60
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2 AWG-300 kcmil
- **Voltage Rating:** 120/240V, 208Y/120, 240V

### Supporting documents:

- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [60 Circuit Plug-On Neutral Loadcenter](#)
- [Eaton Specification Sheet - CH60BPN200N](#)



**Certifications:**

- UL 67
- UL 50

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch main loadcenter

CH60BPN200N

UPC:786685425276

### Dimensions:

- **Height:** 3.88 IN
- **Length:** 45 IN
- **Width:** 14.31 IN

**Notes:** Requires the use of type chnt breakers. Main breaker plug-on neutral loadcenter. 225A max.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Plug-on neutral
- **Type:** Main breaker
- **Amperage Rating:** 200A
- **Box Size:** N
- **Bus Material:** Copper
- **Cover:** Ch8nf- combination, not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 35 kAIC
- **Main Circuit Breaker:** CSH
- **Number Of Circuits:** 60
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2 AWG-300 kcmil
- **Voltage Rating:** 120/240V, 208Y/120, 240V

### Supporting documents:

- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [60 Circuit Plug-On Neutral Loadcenter](#)
- [Eaton Specification Sheet - CH60BPN200N](#)



**Certifications:**

- UL 67
- UL 50

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.