

Eaton CH8L125RP

Catalog Number: CH8L125RP

Eaton CH main lug loadcenters, Cover included, Main lug only, 125A, 7r, Copper, NEMA 3R, Metallic, Overhead, CH, 8, 8, Three-wire, Single-phase, 120/240 V, 208 Y/120, 240 V, #6-1/0 AWG



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH8L125RP
UPC	Product Length/Depth
782114190548	13 in
Product Height	Product Width
3.69 in	11 in
Product Weight	Warranty
12 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Ground bar kits priced separately. Suitable for use as service equipment when not more than two service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Main lug only

Amperage Rating

125 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

8

Number of spaces

8

Phase

Single-phase

Voltage rating

120/240V, 208Y/120, 240V

Wire size

#6-1/0 AWG

Box size

7R

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH8L125RP



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)