

# Specifications

## Eaton CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton CH surge loadcenter
<b>CATALOG NUMBER</b>	CHEC24L125E
<b>UPC</b>	782116200146
<b>PRODUCT LENGTH/DEPTH</b>	32 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	10 in
<b>PRODUCT WEIGHT</b>	7 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	Provision only
<b>TYPE</b>	Main lug only
<b>AMPERAGE RATING</b>	125 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	32
<b>NUMBER OF SPACES</b>	32
<b>PHASE</b>	Single-phase
<b>WIRE SIZE</b>	#6-4/0 AWG
<b>BOX SIZE</b>	E
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kAIC

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>MULTIMEDIA</b>	<a href="#">AFCI Educational Video</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHEC24L125E</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton CH surge loadcenter
<b>CATALOG NUMBER</b>	CHEC24L125E
<b>UPC</b>	782116200146
<b>PRODUCT LENGTH/DEPTH</b>	32 in
<b>PRODUCT HEIGHT</b>	3 in
<b>PRODUCT WIDTH</b>	10 in
<b>PRODUCT WEIGHT</b>	7 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included



Powering Business Worldwide

## Product specifications

<b>SPECIAL FEATURES</b>	Provision only
<b>TYPE</b>	Main lug only
<b>AMPERAGE RATING</b>	125 A
<b>BUS MATERIAL</b>	Aluminum
<b>NUMBER OF CIRCUITS</b>	32
<b>NUMBER OF SPACES</b>	32
<b>PHASE</b>	Single-phase
<b>WIRE SIZE</b>	#6-4/0 AWG
<b>BOX SIZE</b>	E
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kAIC

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1</a>
<b>MULTIMEDIA</b>	<a href="#">AFCI Educational Video</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - CHEC24L125E</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

