

Specifications

Eaton CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG



Photo is representative



General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton CH surge loadcenter |
| CATALOG NUMBER | CHEC24L125E |
| UPC | 782116200146 |
| PRODUCT LENGTH/DEPTH | 32 in |
| PRODUCT HEIGHT | 3 in |
| PRODUCT WIDTH | 10 in |
| PRODUCT WEIGHT | 7 lb |
| WARRANTY | Limited lifetime |
| CERTIFICATIONS | UL Listed |
| CATALOG NOTES | Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included |



Powering Business Worldwide

Product specifications

| | |
|---------------------------|----------------|
| SPECIAL FEATURES | Provision only |
| TYPE | Main lug only |
| AMPERAGE RATING | 125 A |
| BUS MATERIAL | Aluminum |
| NUMBER OF CIRCUITS | 32 |
| NUMBER OF SPACES | 32 |
| PHASE | Single-phase |
| WIRE SIZE | #6-4/0 AWG |
| BOX SIZE | E |
| ENCLOSURE | NEMA 1 |
| INTERRUPT RATING | 25 kAIC |

Resources

| | |
|--------------------------------------|--|
| CATALOGS | Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1 |
| MULTIMEDIA | AFCI Educational Video |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - CHEC24L125E |
| WARRANTY GUIDES | Eaton type CH circuit breaker limited warranty June 2024 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

