



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHM1G9N9NS Pop Metered Surface Mounted

*Eaton Corp*

Catalog Number	CHM1G9N9NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Water and Tamper Resistant Center/Right Receptacle, Metered-Ring, Ground Fault, Non-Ground Fault, Non-Ground Fault, Top, Surface, Circuits: 4, Nema 5-20R2GF, Nema 14-50R, Nema 5-20r2gfi
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

### Dimensions and Weight

Depth	7.2
Height	31
Width	10

### Descriptions

Also Known As...	Meter Box Meter Socket
Description	POP METERED SURFACE MOUNTED
extra long description	ETN CHM1G9N9NS POP METERED, SURFACE
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Water and tamper resistant center/right receptacle, Metered-ring, Ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GF, NEMA 14-50R, NEMA 5-20R2GFI
Product Type	Pop Metered, Surface Mounted
Special Features	Water and tamper resistant center/right receptacle

### Manufacturer Information

Brand	Eaton Corp
GTIN	00786685954394
Manufacturers Part Number	CHM1G9N9NS
UPC	786685954394

### Taxonomies, Classifications, and Categories

Category Description	Meter Sockets
Type	Pedestal mount metered



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	30

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL Listed file E163588,UL 231