

# Eaton CHP14B100X1

Catalog Number: CHP14B100X1

Eaton CH main breaker loadcenters, Main breaker, 100 A, X1, Copper, X1, NEMA 1, Metallic, 10 kAIC, CH, 28, Single-pole, 14, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG, 120/240 V



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CHP14B100X1
<b>UPC</b>	<b>Product Length/Depth</b>
786689055134	18.75 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
11.1 lb	Limited lifetime
<b>Certifications</b>	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Type

Main breaker

### Amperage Rating

100 A

### Bus material

Copper

### Cover

X1

### Main circuit breaker

CH

### Number of circuits

28

### Number Of Poles

Single-pole

### Number of spaces

14

### Phase

Single-phase

### Wire size

#6-1/0 AWG

### Voltage rating

120/240 V

### Box size

X1

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

Two hots, neutral and ground

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP14B100X1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)