

# Eaton CHP22B125R

Catalog Number: CHP22B125R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 125 A, X2, Copper, NEMA 3R, Metallic, CH, 44, 22, Three-wire, Single-phase, Overhead, 120/240 V



## General specifications

### Product Name

Eaton CH main breaker loadcenter

### Catalog Number

CHP22B125R

### UPC

786689058579

### Product Length/Depth

21 in

### Product Height

5.19 in

### Product Width

14.31 in

### Product Weight

22 lb

### Warranty

Limited lifetime

### Certifications

UL 67

UL 50

### Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.



Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Special features

Cover included

### Type

Main breaker

### Amperage Rating

125 A

### Bus material

Copper

### Main circuit breaker

CH

### Number of circuits

44

### Number of spaces

22

### Phase

Single-phase

### Feed type

Overhead

### Voltage rating

120/240 V

### Box size

X2

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP22B125R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)