

# Eaton CHP22N125R

Catalog Number: CHP22N125R

Eaton CH convertible loadcenter, 125A, convertible, 22 spaces, NEMA 3R



## General specifications

### Product Name

Eaton CH convertible loadcenter

### Catalog Number

CHP22N125R

### UPC

786689058586

### Product Length/Depth

21 in

### Product Height

5.19 in

### Product Width

14.31 in

### Product Weight

22 lb

### Warranty

Limited lifetime

### Certifications

UL 67

UL 50

### Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

## defaultTaxonomyAttributeLabel

### Special features

Cover included

### Type

Converible

### Amperage Rating

125 A

### Bus material

Copper

### Feed type

Overhead

### Number of spaces

22

### Phase

Single-phase

### Box size

X2

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP22N125R](#)