

Eaton CHP22N125X2

Catalog Number: CHP22N125X2

Eaton CH PON 3/4-inEaton CH loadcenter, 125A, convertible, 22 spaces



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP22N125X2
UPC	Product Length/Depth
786679189726	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
11.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 50	Purchase Size X2 Cover Separately
UL 67	

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

125 A

Bus material

Copper

Cover

X2

Feed type

Top/bottom

Number of circuits

22

Number of spaces

22

Phase

Single-phase

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP22N125X2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)