

# Eaton CHP24L150R

Catalog Number: CHP24L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 48, 24, Three-wire, Single-phase



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main lug loadcenter	CHP24L150R
<b>UPC</b>	<b>Product Length/Depth</b>
786689058623	29 in
<b>Product Height</b>	<b>Product Width</b>
5.19 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
26 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

## Product specifications

### Special features

Cover included

### Type

Main Lug Only

### Amperage Rating

150 A

### Bus material

Copper

### Feed type

Overhead

### Number of circuits

48

### Number of spaces

24

### Phase

Single-phase

### Box size

X5

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP24L150R](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHP24L150R

Catalog Number: CHP24L150R

Eaton CH main lug loadcenters,Cover included,Main Lug Only,150A,X5,Copper,NEMA 3R,Metallic,Overhead,48,24,Three-wire,Single-phase



Photo is representative

## General specifications

### Product Name

Eaton CH main lug loadcenter

### Catalog Number

CHP24L150R

### UPC

786689058623

### Product Length/Depth

29 in

### Product Height

5.19 in

### Product Width

14.31 in

### Product Weight

26 lb

### Warranty

Limited lifetime

### Certifications

UL 67

UL 50

### Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

## Product specifications

### Special features

Cover included

### Type

Main Lug Only

### Amperage Rating

150 A

### Bus material

Copper

### Feed type

Overhead

### Number of circuits

48

### Number of spaces

24

### Phase

Single-phase

### Box size

X5

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP24L150R](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)