

# Eaton CHP32L150X5

Catalog Number: CHP32L150X5

Eaton CH main lug loadcenters, PON, CH, 150 A, X5, Copper, I, NEMA 1 indoor, Steel, 25 kAIC, 64, 32, 3, Single-phase, 120/240 V, #4 AWG-300 kcmil



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main lug loadcenter	CHP32L150X5
<b>UPC</b>	<b>Product Length/Depth</b>
786689054298	29 in
<b>Product Height</b>	<b>Product Width</b>
4 in	14.3 in
<b>Product Weight</b>	<b>Certifications</b>
15.8 lb	UL 67

## Catalog Notes

Purchase Size X5 Cover Separately

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

CH

### Amperage Rating

150 A

### Bus material

Copper

### Number of circuits

64

### Number of spaces

32

### Phase

Single-phase

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 1

### Enclosure material

Steel

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP32L150X5](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHP32L150X5

Catalog Number: CHP32L150X5

Eaton CH main lug loadcenters, PON, CH, 150 A, X5, Copper, I, NEMA 1 indoor, Steel, 25 kAIC, 64, 32, 3, Single-phase, 120/240 V, #4 AWG-300 kcmil



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main lug loadcenter	CHP32L150X5
<b>UPC</b>	<b>Product Length/Depth</b>
786689054298	29 in
<b>Product Height</b>	<b>Product Width</b>
4 in	14.3 in
<b>Product Weight</b>	<b>Certifications</b>
15.8 lb	UL 67

## Catalog Notes

Purchase Size X5 Cover Separately

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

CH

### Amperage Rating

150 A

### Bus material

Copper

### Number of circuits

64

### Number of spaces

32

### Phase

Single-phase

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 1

### Enclosure material

Steel

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP32L150X5](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)