

# Eaton CHP42B200V29

Catalog Number: CHP42B200V29

Eaton CH main breaker loadcenters, PON, Main breaker, 200 A, X7, Copper, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 84, 42, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG, 120/240 V

## General specifications

Product Name	Eaton CH main breaker loadcenter	Catalog Number	CHP42B200V29
UPC	786689058401	Product Length/Depth	38 in
Product Height	4.1 in	Product Width	15.31 in
Product Weight	35.2 lb	Warranty	Limited lifetime
Certifications	UL 67 UL 50	Catalog Notes	Value Pack #V29, (2) CHF120 & (1) CHF230



## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

Main breaker

### Amperage Rating

200 A

### Bus material

Copper

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

84

### Number of spaces

42

### Phase

Single-phase

### Wire size

#6-1/0 AWG

### Voltage rating

120/240 V

### Box size

X7

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

Two hots, neutral and ground

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP42B200V29](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton CHP42B200V29

Catalog Number: CHP42B200V29

Eaton CH main breaker loadcenters, PON, Main breaker, 200 A, X7, Copper, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 84, 42, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG, 120/240 V

## General specifications

Product Name	Eaton CH main breaker loadcenter	Catalog Number	CHP42B200V29
UPC	786689058401	Product Length/Depth	38 in
Product Height	4.1 in	Product Width	15.31 in
Product Weight	35.2 lb	Warranty	Limited lifetime
Certifications	UL 67 UL 50	Catalog Notes	Value Pack #V29, (2) CHF120 & (1) CHF230



## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

Main breaker

### Amperage Rating

200 A

### Bus material

Copper

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

84

### Number of spaces

42

### Phase

Single-phase

### Wire size

#6-1/0 AWG

### Voltage rating

120/240 V

### Box size

X7

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

Two hots, neutral and ground

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP42B200V29](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)