

Eaton CHP42B200V29

Catalog Number: CHP42B200V29

Eaton CH main breaker loadcenters,PON,Main breaker,200 A,X7,Copper,Cover included,NEMA 1,Metallic,25 kAIC,CSR,84,42,Two hots, a neutral and a ground,Single-phase,#6-1/0 AWG,120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP42B200V29
UPC	Product Length/Depth
786689058401	38 in
Product Height	Product Width
4.1 in	15.31 in
Product Weight	Warranty
35.2 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Value Pack #V29, (2) CHF120 & (1)
UL 50	CHF230

defaultTaxonomyAttributeLabel	Resources
<p>Special features</p> <p>PON</p>	<p>Brochures</p> <p>Loadcenters and Circuit Breakers</p>
<p>Type</p> <p>Main breaker</p>	<p>Multimedia</p> <p>AFCI Educational Video</p>
<p>Amperage Rating</p> <p>200 A</p>	<p>Specifications and datasheets</p> <p>Eaton Specification Sheet - CHP42B200V29</p>
<p>Bus material</p> <p>Copper</p>	<p>Warranty guides</p> <p>Eaton type CH circuit breaker limited warranty June 2024</p>
<p>Cover</p> <p>Cover included</p>	
<p>Main circuit breaker</p> <p>CSR</p>	
<p>Number of circuits</p> <p>84</p>	
<p>Number of spaces</p> <p>42</p>	
<p>Phase</p> <p>Single-phase</p>	
<p>Wire size</p> <p>#6-1/0 AWG</p>	
<p>Voltage rating</p> <p>120/240 V</p>	
<p>Box size</p> <p>X7</p>	
<p>Enclosure</p> <p>NEMA 1</p>	
<p>Enclosure material</p> <p>Metallic</p>	
<p>Interrupt rating</p> <p>25 kAIC</p>	
<p>Number of wires</p> <p>Two hots, neutral and ground</p>	



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia