

Eaton CHP42B200V29

Catalog Number: CHP42B200V29

Eaton CH main breaker loadcenters, PON, Main breaker, 200 A, X7, Copper, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 84, 42, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG, 120/240 V

General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP42B200V29
UPC	Product Length/Depth
786689058401	38 in
Product Height	Product Width
4.1 in	15.31 in
Product Weight	Warranty
35.2 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Value Pack #V29, (2) CHF120 & (1)
UL 50	CHF230



defaultTaxonomyAttributeLabel

Special features

PON

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

84

Number of spaces

42

Phase

Single-phase

Wire size

#6-1/0 AWG

Voltage rating

120/240 V

Box size

X7

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP42B200V29](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia