

Eaton CHP42L225X6

Catalog Number: CHP42L225X6

Eaton CH main lug loadcenters, PON, Main Lug Only, 225 A, X6, Copper, NEMA 1, Metallic, 10 kAIC, 84, Single-pole, 42, Two hots, a neutral and a ground, Single-phase, 120/240 V, #4 AWG-300 kcmil



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP42L225X6
UPC	Product Length/Depth
786689055202	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
18.5 lb	Limited lifetime
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

PON

Type

Main Lug Only

Amperage Rating

225 A

Bus material

Copper

Number of circuits

84

Number Of Poles

Single-pole

Number of spaces

42

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#1 AWG-300 kcmil

Box size

X6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP42L225X6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)