

Eaton CHP42N225R

Catalog Number: CHP42N225R

Eaton CH plug-on neutral loadcenter, 225A, convertible, 42 spaces, NEMA 3R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP42N225R
UPC	Product Length/Depth
786689058746	37 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
32 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Convertible

Amperage Rating

225 A

Bus material

Copper

Feed type

Overhead

Number of spaces

42

Phase

Single-phase

Box size

X7

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP42N225R](#)