

Eaton CHPX0AS

Catalog Number: CHPX0AS

Eaton CH Indoor Combination Cover, Surface or flush universal applications, Type CH indoor combination cover, 125 A, X0, Sandlewood, NEMA 1, CH, Surface, flush, 12 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V

General specifications



Product Name
Eaton CH cover

UPC
786689162276

Product Height
16.75 in

Product Weight
5.6 lb

Certifications

Contact Manufacturer

Catalog Number
CHPX0AS

Product Length/Depth
1 in

Product Width
14.31 in

Warranty
Limited lifetime

Photo is representative

defaultTaxonomyAttributeLabel

Special features

Surface or flush universal applications

Type

Cover

Amperage Rating

225 A

Bus material

Aluminum

Mounting

Surface, flush

Number of spaces

12

Phase

Three-phase

Used with

CH Breakers

Voltage rating

120/240 V

Box size

X0

Color

Sandalwood

Enclosure

NEMA 1

Interrupt rating

10 kAIC

Size

CH - 3/4 in - plug on neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHPX0AS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)