

# Eaton CHPX6BS

Catalog Number: CHPX6BS

Eaton CH Surface Cover, Surface or flush universal applications, Type CH surface cover, 150 A, X6, Sandlewood, NEMA 1, CH, Surface, flush, 32 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V



## General specifications

|                       |                             |
|-----------------------|-----------------------------|
| <b>Product Name</b>   | <b>Catalog Number</b>       |
| Eaton CH cover        | CHPX6BS                     |
| <b>UPC</b>            | <b>Product Length/Depth</b> |
| 786689162405          | 1 in                        |
| <b>Product Height</b> | <b>Product Width</b>        |
| 34.12 in              | 14.31 in                    |
| <b>Product Weight</b> | <b>Warranty</b>             |
| 11.5 lb               | Limited lifetime            |
| <b>Certifications</b> |                             |
| Contact Manufacturer  |                             |

## defaultTaxonomyAttributeLabel

### Special features

Surface or flush universal applications

### Type

Cover

### Amperage Rating

225 A

### Bus material

Aluminum

### Mounting

Surface, flush

### Number of spaces

32

### Phase

Three-phase

### Used with

CH Breakers

### Voltage rating

120/240 V

### Box size

X6

### Color

Sandalwood

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

### Size

CH - 3/4 in - plug on neutral

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHPX6BS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)