

Eaton CHPX6LF

Catalog Number: CHPX6LF

Eaton CH Flush Cover, Flush-mount applications, Type CH flush cover, 225 A, X6, Sandlewood, NEMA 1, CH, Flush, 42 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V

General specifications



Photo is representative

Product Name

Eaton CH cover

UPC

786689162412

Product Height

35.12 in

Product Weight

11.8 lb

Certifications

Contact Manufacturer

Catalog Number

CHPX6LF

Product Length/Depth

1 in

Product Width

15.31 in

Warranty

Limited lifetime

defaultTaxonomyAttributeLabel

Special features

Flush-mount applications

Type

Cover

Amperage Rating

225 A

Bus material

Aluminum

Mounting

Flush

Number of spaces

42

Phase

Single-phase

Used with

CH Breakers

Voltage rating

120/240 V

Box size

X6

Color

Sandalwood

Enclosure

NEMA 1

Interrupt rating

10 kAIC

Size

CH - 3/4 in - plug on neutral

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHPX6LF



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)