

Eaton CHPX7NF

Catalog Number: CHPX7NF

Eaton CH Combination Cover, Flush-mount applications, Type CH combination cover, 225 A, X7, Sandlewood, NEMA 1, CH, Flush, 42 Spaces, Three-wire, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V

General specifications



Photo is representative

Product Name
Eaton CH cover

UPC
786689162467

Product Height
38 in

Product Weight
12.8 lb

Certifications

Contact Manufacturer

Catalog Number
CHPX7NF

Product Length/Depth
1 in

Product Width
15.31 in

Warranty
Limited lifetime

defaultTaxonomyAttributeLabel

Special features

Flush-mount applications

Type

Cover

Amperage Rating

225 A

Bus material

Aluminum

Mounting

Flush

Number of spaces

42

Phase

Three-phase

Used with

CH Breakers

Voltage rating

120/240 V

Box size

X7

Color

Sandalwood

Enclosure

NEMA 1

Interrupt rating

10 kAIC

Size

CH - 3/4 in - plug on neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHPX7NF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)