

# Eaton CHPX9BS

Catalog Number: CHPX9BS

Eaton CH Indoor Combination Cover, Surface or flush universal applications, Type CH indoor combination cover, 225 A, X9, Sandalwood, NEMA 1, CH, Surface, flush, 60 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH cover	CHPX9BS
<b>UPC</b>	<b>Product Length/Depth</b>
786689162245	1 in
<b>Product Height</b>	<b>Product Width</b>
45 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
15.2 lb	Limited lifetime
<b>Certifications</b>	
<b>Contact Manufacturer</b>	

## defaultTaxonomyAttributeLabel

### Special features

Surface or flush universal applications

### Type

Cover

### Amperage Rating

225 A

### Bus material

Aluminum

### Mounting

Surface, flush

### Number of spaces

60

### Phase

Three-phase

### Used with

CH Breakers

### Voltage rating

120/240 V

### Box size

X9

### Color

Sandalwood

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

### Size

CH - 3/4 in - plug on neutral

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHPX9BS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)