

Eaton CHQ240

Catalog Number: CHQ240

3/4" Thermal magnetic circuit breakers, Type CHQ 3/4-Inch classified replacement breaker clamshell pack, Ground fault, 40 A, 10 kAIC, Two-pole, 120/240V, CHQ, Common breaker trip, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, Q30, CHQ, Type CH Loadcenters

General specifications

| | |
|--|--|
| Product Name | Catalog Number |
| Eaton Classified 3/4" thermal magnetic circuit breaker | CHQ240 |
| | UPC |
| | 782113010946 |
| Product Length/Depth | Product Height |
| 2.5 in | 3 in |
| Product Width | Product Weight |
| 1.5 in | 0.6 lb |
| Warranty | Certifications |
| Limited lifetime residential, 1 year commercial | UL 489 |
| | Catalog Notes |
| | Replacement for Square D Type QO Breakers. Requires two 3/4-inch (19.1 mm) spaces. |



defaultTaxonomyAttributeLabel

Type

Type CHQ 3/4-Inch classified replacement breaker clamshell pack

Special features

Ground fault

Amperage Rating

40 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CHQ

Wire size

(2) #14-10 AWG Cu/Al

(1) #14-8 AWG

Number of poles

Two-pole

Quantity

30

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Standard circuit breaker catalog numbers - 5651B63SH09](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHQ240](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)