

Eaton CHR9N9NSU

Catalog Number: CHR9N9NSU

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: None, Circuits: 4, Weather and tamper resist center and left receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA 5-20R2GFI WR TR, Right: None, Ringless

General specifications



Photo is representative

Product Name

Eaton pedestal mount metered

Catalog Number

CHR9N9NSU

UPC

786685404219

Product Length/Depth

30.5 in

Product Height

7 in

Product Width

10 in

Product Weight

30 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231

UL Listed file E163588

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

None

Feed type

Bottom

Mounting

Surface

Number of circuits

4

Receptacle center

NEMA 5-20R2GF

Receptacle left

NEMA 5-20R2GFI

Receptacle right

None

Type

Metered-ringless

Miscellaneous

Special features

Water and tamper resistant left/center receptacle

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CHR9N9NSU



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia