

Eaton CHSPT2MICRO

Catalog Number: CHSPT2MICRO

SPD Type 2 CHSP Service Entrance Surge Protection, 120/240V line, 150V L-N, 300V L-L MCOV, 600V L-N, 1000V L-L, 800V N-G, 600V L-G VPR, 22 kA SCCR, NEMA 4 enclosure, Single-phase, 60 Hz, 5 kA nominal current discharge, 36 kA surge current

General specifications



Product Name	Catalog Number
Eaton CHSPT2 surge protection device	CHSPT2MICRO
UPC	Product Length/Depth
786685436869	2.5 in
Product Height	Product Width
10 in	3 in
Product Weight	Certifications
1 lb	UL 1449 cUL Certified UL Recognized

Catalog Notes

5kA nominal discharge current. Has 36kA one time surge current rating.

defaultTaxonomyAttributeLabel

Type

Surge protection device

Special features

Meets or exceeds the requirements specified in IBC ©2006, CBC2007, and UBC@Zone 4

Frequency rating

60 Hz

Interrupt rating

200 kAIC

Nominal Discharge Current

5 kA

Operating voltage

150V L-N, 300V L-L

Protection

600V L-N, 1000V L-L, 800V N-G, 600V L-G

Voltage rating

120/240 V

Enclosure

NEMA 4

Phase

Single-phase

Surge current

36 kA

Short-circuit rating

22000 kA

Operating temperature

-40 to 50 °C

Resources

Brochures

[Storm season is coming. Are you prepared?](#)

[Mike Holmes - Type 2 Surge Products](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Installation instructions

[Complete Home Surge Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - CHSPT2MICRO](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)