

# Specifications



## Eaton CHU1N7N4NS

Eaton pedestal mount unmetered, Unmetered, 50A, 20A, 30A, Non-ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 14-50R, NEMA 5-20R2GFI, NEMA TT-30R, 4, 3, 3, 125/250V, 125V, 125V

### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount unmetered
<b>CATALOG NUMBER</b>	CHU1N7N4NS
<b>UPC</b>	782114203828
<b>PRODUCT LENGTH/DEPTH</b>	4.3 in
<b>PRODUCT HEIGHT</b>	17.1 in
<b>PRODUCT WIDTH</b>	9.5 in
<b>PRODUCT WEIGHT</b>	16 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL 231 UL Listed file E163588

## Product specifications

TYPE	Unmetered
CIRCUIT BREAKER POSITION 1	Non-ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	Non-ground fault
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA TT-30R
FEED TYPE	Top
MOUNTING	Surface
NUMBER OF CIRCUITS	4

## Resources

CATALOGS	<a href="#">Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CHU1N7N4NS</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

