

Eaton pedestal mount unmetered

CHU1N9N4NPTZ

UPC:786680206795

Dimensions:

- **Height:** 39.9 IN
- **Length:** 6.8 IN
- **Width:** 9.5 IN

Weight:45 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Factory installed pedestal extension with lay-in ground lug
- **Type:** Unmetered
- **Circuit Breaker Position 1:** Non-ground fault
- **Feed Type:** Top
- **Mounting:** Pedestal
- **Number Of Circuits:** 4
- **Receptacle Center:** NEMA 5-20R2GFI/weather and tamper resistant
- **Receptacle Left:** NEMA 14-50R
- **Receptacle Right:** NEMA TT-30R

Supporting documents:

- [Eaton Specification Sheet - CHU1N9N4NPTZ](#)

Certifications:

- UL 231
- UL Listed file E163588

Product compliance: No Data



Eaton pedestal mount unmetered

CHU1N9N4NPTZ

UPC:786680206795

Dimensions:

- **Height:** 39.9 IN
- **Length:** 6.8 IN
- **Width:** 9.5 IN

Weight:45 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Factory installed pedestal extension with lay-in ground lug
- **Type:** Unmetered
- **Circuit Breaker Position 1:** Non-ground fault
- **Feed Type:** Top
- **Mounting:** Pedestal
- **Number Of Circuits:** 4
- **Receptacle Center:** NEMA 5-20R2GFI/weather and tamper resistant
- **Receptacle Left:** NEMA 14-50R
- **Receptacle Right:** NEMA TT-30R

Supporting documents:

- [Eaton Specification Sheet - CHU1N9N4NPTZ](#)

Certifications:

- UL 231
- UL Listed file E163588

Product compliance: No Data



