

Eaton CHU1N9N4NPTZ

Catalog Number: CHU1N9N4NPTZ

Eaton pedestal mount unmetered, Ped. ext. w/ lay-in ground lug, Unmetered, 50A, 20A, 30A, Non-GF, Non-GF, Non-GF, Top, Pedestal, Circuits: 4, NEMA 14-50R, NEMA 5-20R2GFI/weather and tamper resis., NEMA TT-30R, 4, 3, 3, 125/250V, 125V, 125V



General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU1N9N4NPTZ
UPC	Product Length/Depth
786680206795	6.8 in
Product Height	Product Width
39.9 in	9.5 in
Product Weight	Warranty
45 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231
UL Listed file E163588

defaultTaxonomyAttributeLabel

Special features

Factory installed pedestal extension with lay-in ground lug

Type

Unmetered

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Receptacle center

NEMA 5-20R2GFI WRTR

Receptacle left

NEMA 14-50R

Receptacle right

NEMA TT-30R

Feed type

Top

Mounting

Pedestal

Number of circuits

4

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHU1N9N4NPTZ](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)