Specifications







Eaton CHU4N7NS

Eaton pedestal mount unmetered, Unmetered, 30A, 20A, None, Non-ground fault, Nonground fault, Nonground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None

General specifications	
PRODUCT NAME	Eaton pedestal mount unmetered
CATALOG NUMBER	CHU4N7NS
UPC	782114203743
PRODUCT LENGTH/DEPTH	13.6 in
PRODUCT HEIGHT	39.9 in
PRODUCT WIDTH	9.5 in
PRODUCT WEIGHT	8.6 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed file E163588 UL 231



Product specifications	S
ТҮРЕ	Unmetered
CIRCUIT BREAKER POSITION 1	Non-ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	None
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA TT-30R
RECEPTACLE RIGHT	None
FEED TYPE	Тор
MOUNTING	Surface
NUMBER OF CIRCUITS	4

Resources	
CATALOGS	Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHU4N7NS

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc

© 2025 Eaton. All Rights

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.







