

Eaton CHU6G6G5GS

Catalog Number: CHU6G6G5GS

Eaton pedestal mount unmetered, 20A, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2, NEMA 6-20R2, 3, 125V, 250V

General specifications



Product Name

Eaton pedestal mount unmetered

Catalog Number

CHU6G6G5GS

UPC

782114203927

Product Length/Depth

4.3 in

Product Height

17.1 in

Product Width

9.5 in

Product Weight

16.25 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588

UL 231

Physical Attributes

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Ground fault

Circuit breaker position 3

Ground fault

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle center

NEMA 5-20R2

Receptacle left

NEMA 5-20R2

Receptacle right

NEMA 6-20R2

Type

Unmetered

Resources

Catalogs

Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5

Specifications and datasheets

Eaton Specification Sheet - CHU6G6G5GS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)