

# Eaton CHU7N7N5NS

Catalog Number: CHU7N7N5NS

Eaton pedestal mount unmetered, 20A, Non-ground fault, Top, Surface, Circ: 4, NEMA 6-20R2, 3, 125V, 250V

## General specifications



|                                |  |
|--------------------------------|--|
| <b>Product Name</b>            | <b>Catalog Number</b>  |
| Eaton pedestal mount unmetered | CHU7N7N5NS   |
| <b>UPC</b>                     | <b>Product Length/Depth</b>  |
| 782114203941                   | 18.2 in  |
| <b>Product Height</b>          | <b>Product Width</b>   |
| 7.9 in                         | 10 in  |
| <b>Product Weight</b>          | <b>Warranty</b>  |
| 16 lb                          | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |

## Certifications

UL 231  
UL Listed file E163588

## Product specifications

### Type

Unmetered

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Non-ground fault

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA 5-20R2GFI

### Receptacle right

NEMA 6-20R2

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

## Resources

### Catalogs

Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5

### Specifications and datasheets

Eaton Specification Sheet - CHU7N7N5NS



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia