



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CJ5E88TGWH Mini Module *Panduit Corporation*

Catalog Number	CJ5E88TGWH
Manufacturer	Panduit Corporation
Description	The Mini-Com® Cat 5E Utp RJ45 TG-Style Jack Module Is Designed to Terminate 4-Pair, 22-26 Awg Twisted Pair Cable. Each Module Is 100% Factory Tested For Continuity. Contacts Are Plated With 50 Microinches Of Gold For Superior Performance. Jack Modules Are Compatible With Mini-Com Modular Patch Panels and Faceplates. The Jack Module Is White.
Weight per unit	0.0260 (lbs/each)
Product Category	20080923104515

Features

Cable Entry	T568A/T568B
Material	ABS/Plastic
media	Yes

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Depth	1.5
Width	0.62

Descriptions

Description	MINI MODULE
extra long description	PAN CJ5E88TGWH Mini-Com® UTP RJ45 C
Long Description	The Mini-Com® Cat 5e UTP RJ45 TG-Style Jack Module is designed to terminate 4-pair, 22-26 AWG twisted pair cable. Each module is 100% factory tested for continuity. Contacts are plated with 50 microinches of gold for superior performance. Jack modules are compatible with Mini-Com Modular Patch Panels and Faceplates. The jack module is White.
Product Type	Mini-Com® Utp RJ45 Cat 5E TG Jack Module, White

Manufacturer Information

Brand	PANDUIT
GTIN	00074983395385
Manufacturers Part Number	CJ5E88TGWH
Model	Mini-Com®
UPC	074983395385



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	JACK MODULE

Packaging

Carton	1
Package	25
Weight Per each	0.026

Uses, Certifications, and Standards

Application	Unshielded
standard	Exceeds Channel and Component Requirements of ANSI/TIA-568.2-D and ISO 11801 Standards for the Respective Category, Meets IEC 60603-7, Supports 2500 Connection Cycles with IEEE 802.3af / 802.3at and 802.3bt Type 3 and Type 4, UL 1863 and UL 2043 and RoHS C