

Specifications



Eaton CJA410

Eaton Crouse-Hinds series PowerMate CJA back box, 60A/100A/150A, Cast aluminum, 1-1/4", 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CJA back box
CATALOG NUMBER	CJA410
UPC	662276277014
PRODUCT LENGTH/DEPTH	7.44 in
PRODUCT HEIGHT	8 in
PRODUCT WIDTH	5.88 in
PRODUCT WEIGHT	2.2 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

Product specifications

AMPERAGE RATING	60A/100A/150A
TRADE SIZE	1-1/4"
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Cast aluminum

Resources

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds CJA410 3D drawing](#)

BROCHURES [PowerMate Drilling Pin and Sleeve Devices brochure](#)

CATALOGS [PowerMate Drilling Pin and Sleeve Devices catalog page](#)

SPECIFICATIONS AND DATASHEETS [PowerMate Connectors](#)

[Eaton Specification Sheet - CJA410](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

