

Eaton CLGF120

Catalog Number: CLGF120

Eaton Classified 1" GFCI circuit breaker, Ground fault circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, CLGF, Trip-to-center, Plug-on, #14-8 AWG, Ground fault circuit interrupter, GFI



General specifications

Product Name	Catalog Number
Eaton Classified 1" GFCI circuit breaker	CLGF120
UPC	Product Length/Depth
786689031527	4 in
Product Height	Product Width
1 in	3.5 in
Product Weight	Certifications
0.45 lb	Contact Manufacturer

defaultTaxonomyAttributeLabel

Type

Ground fault circuit breaker

Amperage Rating

20 A

Voltage rating

120/240 V

Trip Type

Trip-to-center

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

CLGF

Connection

Plug-on

Wire size

#14-8 AWG

Number of poles

Single-pole

Trip rating

15 A

Resources

Brochures

Loadcenters and Circuit Breakers

Standard circuit breaker catalog numbers - 5651B63SH09

Specifications and datasheets

Eaton Specification Sheet - CLGF120



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)