



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CMH70TU830G12 70W MH LMP

*Ge By Current Lamps*

Catalog Number	CMH70TU830G12
Manufacturer	Ge By Current Lamps
Description	Ge Constantcolor®, 70 WTT, 6200 LM, 3000 KV, 83 Cri, Bi-Pin (G12) Base, 15000 HR Average Life
Weight per unit	0.5800 (lbs/each)
Product Category	Hid Ceramic Metal Halide Lamps

### Features

average life	15000
Base	Bi-Pin (G12)
lumens	6200
Wattage	70

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	83
color temperature	3000
Finish	Clear
Style	Enclosed fixtures only

### Descriptions

Description	70W MH LMP
extra long description	GEL CMH70TU/830/G12 20016 MULTIVAPO
Long Description	GE ConstantColor®, 70 WTT, 6200 LM, 3000 KV, 83 CRI, Bi-Pin (G12) Base, 15000 HR Average Life
Product Type	20016 Multivapor
Special Features	3.93IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168200165
Manufacturers Part Number	CMH70TU/830/G12
UPC	043168200165

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	12
Weight Per each	0.58

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------