



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CPR24 1-1/4" Rigid Coupling Threadless *Crouse-Hinds*

Catalog Number	CPR24
Manufacturer	Crouse-Hinds
Description	Threadless Coupling, 1-1/4 In Trade Size, CPR Model, Straight, 85 LB/100
Weight per unit	0.8100 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

dimensions	2.6300 IN X 2.3800 IN X 2.3800 IN
Material	Malleable Iron

### Descriptions

Description	1-1/4" RIGID COUPLING THREADLESS
extra long description	MIDWEST CPR24 1 1/4 RGD CMP CPL
Features	Crouse-Hinds series rigid/IMC connectors, couplings and combination couplings are used to join used to join rigid/IMC conduit to a box or enclosure, or to couple two ends of conduit together. Our rigid/IMC connectors and couplings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in a variety of materials to suit customer preferences, including malleable iron, steel, zinc die cast, aluminum, stainless steel and hot dip galvanized mallea

### Manufacturer Information

Brand	Eaton
GTIN	00784564122247
UPC	784564122247

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression coupling

### Packaging

Carton	5
Weight Per each	0.81

### Uses, Certifications, and Standards

standard	UL 514B, CUL
----------	--------------