



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CPR28 3" Rigid Coupling Threadless *Crouse-Hinds*

Catalog Number	CPR28
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series CPR Compression Coupling, Rigid/Imc, Malleable Iron, Compression Type, 3"
Weight per unit	4.5 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

dimensions	5.2000 IN X 5.6000 IN X 5.6000 IN
Material	Malleable Iron

### Descriptions

Description	3" RIGID COUPLING THREADLESS
extra long description	MIDWEST CPR28 3 RGD CMP CPL
Features	Crouse-Hinds series rigid/IMC connectors, couplings and combination couplings are used to join used to join rigid/IMC conduit to a box or enclosure, or to couple two ends of conduit together. Our rigid/IMC connectors and couplings are available in set screw type and compression type, in both insulated and non-insulated versions. They are available in a variety of materials to suit customer preferences, including malleable iron, steel, zinc die cast, aluminum, stainless steel and hot dip galvanized mallea
Long Description	Eaton Crouse-Hinds series CPR compression coupling, Rigid/IMC, Malleable iron, Compression type, 3"
Product Type	3 RGD CMP CPL
Special Features	Concrete Tight

### Manufacturer Information

Brand	Eaton
GTIN	00784564122285
Manufacturers Part Number	CPR28
UPC	784564122285

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Compression coupling

### Packaging

Carton	1
Weight Per each	4.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /  
Institutional Buildings / Structures - Other

standard

UL 514B, CUL